

Suitable for work on hard and tough materials, e.g. titanium and titanium alloys. It is also ideally suitable for work on copper and bronze.

The SiC abrasive produces a particularly fine surface finish.

Abrasive: Silicon carbide SiC


Ordering example:
EAN 4007220155943
F 6030/6 SiC 60


Please complete the description with the desired grit size.

PFERDERGONOMICS®:



Mounted flap wheels
Silicon carbide SiC



Description	Grit size				D x T [mm]	Acc. to ISO standards	Recom. speed [RPM]	Max. perm. speed [RPM]	
	60	80	120	150					
	EAN 4007220								

Shank dia. 6 x 40 mm [S_d x L]

F 3010/6 SiC	154588	154595	154601	154618	30 x 10	3919	12,000	25,400	10
F 6030/6 SiC	155943	155950	155967	155974	60 x 30	3919	6,300	12,700	10

The content of the set is based on the most common applications in industry and crafts.

The sales-promoting display box for shops contains 40 mounted flap wheels of the aluminium oxide A type, with shank diameter 6 mm.


Contents:

5 pcs. each of mounted flap wheels:

- F 4015/6 A 80
- F 4015/6 A 120
- F 5015/6 A 60
- F 5015/6 A 80
- F 6030/6 A 60
- F 6040/6 A 80
- F 6040/6 A 150
- F 8030/6 A 60

Mounted flap wheel set



Description	EAN 4007220	Dimensions [mm]	
FSO 5400	156087	240 x 145 x 240	1



204
205
206